

SHA45A

(Reducer type: SG type)

ENCODER CONNECTOR
 HOUSING :1-1903130-4
 TAB CONTACT :1903117-2
 ITE Connectivity (AMP) I

MOTOR/BRAKE CONNECTOR
 HOUSING :350715-1
 PIN CONTACT (MOTOR U·V·W) :350547-1
 PIN CONTACT (BRAKE) :350690-1
 PIN CONTACT (MOTOR PE) :350669-1
 ITE Connectivity (AMP) I

OUTPUT ROTATIONAL PART




REMARK.3

R0.4 MAX

15 MAX

HOLLOW SHAFT DIAMETER
 (φ14.3)

Unit: mm



Notice:
 All specifications and dimensions shown in the drawing are subject to change without notice. This drawing is the property of Harmonic Drive LLC. This data is believed to be accurate, however, Harmonic Drive LLC assumes no liability for any errors or omissions in the specifications, models or drawings.

Harmonic Drive LLC
 Tel: 800-921-3332
 www.harmonicdrive.net



Harmonic Drive LLC
 800-921-3332
 www.harmonicdrive.net