



REMARKS

Lubrication : Harmonic Drive Harmonic Grease SK-2
 Cross Roller Bearing Harmonic Grease 4B No.2
 Designing and/or Handling of Harmonic Drive Gears (Harmonic Actuators)
 has to comply with technical information shown in Harmonic Drive Catalog.

| Rated Torque at 2000r/min | Limit for Repeated Peak Torque | Limit for Average Torque | Limit for Momentary Peak Torque |
|---------------------------|--------------------------------|--------------------------|---------------------------------|
| 5.4 N·m | 19 N·m | 7.7 N·m | 35 N·m |

| |
|----------------------|
| CUSTOMER DRAWING NO. |
| |
| |
| |

PROPRIETORSHIP
 This drawing (document) is the **PROPERTY** of Harmonic Drive Systems, Inc. and shall not be traced, otherwise copied or used for purposes other than agreed upon, nor communicated to any third party without written permission of Harmonic Drive Systems, Inc.

| | | | | | | | | | | | | |
|--|----------|-------------------|------------------------------|-----------|-------------|--------------|--------------|--|--|------------------|-------------------|-------------|
| 訂正 REV | △ | 来歴 DESCRIPTION | Correction of misdescription | | | 設計 DESIGN | S.Momose | Oct-26-'12 | タイトル TITLE | ASSEMBLY DRAWING | | |
| 仕様 SPEC | | | | | 尺度 SCALE | 1:1 | 検図 VRFD | H.Tukahara | Oct-26-'12 | 製品名 ARTICLE | SHD-14-100-2UH-LW | |
| 機械加工 無記号公差 | 0 0.5 | 0.5 6 | 6 30 | 30 120 | 120 315 | 315 1000 | 1000 2000 | 備考 REMARKS | 特記無き角はC0.2以下、すみの丸みはR0.4以下 | | | |
| GENERAL TOLERANCE | ±0.05 | ±0.1 | ±0.2 | ±0.3 | ±0.5 | ±0.8 | ±1.2 | 無記号表面 SURFACES MARKED EXCEPT AS NOTED | 50S | 25S | 6.3S | |
| 本図は(株)ハーモニック・ドライブ・システムの所有に係わるものです。許可なく第三者に見せたり、トレースその他の複写及び指定された用途以外には使用しないで下さい。 | | | DWG SIZE | A3 | UNIT | mm | THIRD ANG | | HARMONIC DRIVE SYSTEMS INC TOKYO JAPAN | | 図番 DWG No | C2A4385 - A |